



Rack PDU 2G, Metered-by-Outlet, ZeroU, 16A, 230V, (21) C13 & (3) C19

AP8459EU3

Overview

Presentation APC Metered by Outlet Rack Power Distribution Units (PDUs) provide individual outlet power metering to enable energy optimization and circuit protection. Current metering provides real-time remote monitoring of connected loads. Metered by Outlet Rack PDUs provide power utilization data to allow Data Center Managers to make informed decisions on load balancing and right sizing IT environments to lower total cost of ownership. Metered by Outlet Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and ultra low profile circuit breakers. Users can access and configure Metered by Outlet Rack PDUs through secure Web, SNMP, or Telnet Interfaces which are complimented by APC Centralized Management platforms using InfraStruxure Central, Operations, Capacity, and Energy Efficiency. Lead Time

Usually in Stock

Main

Colour	Black
Pdu Type	Metered outlet
Cord Length	3.00 m
Provided Equipment	CAN port terminator Installation guide Rack mounting brackets Safety guide Serial configuration cable

Complementary

Input Voltage	200 V 208 V 230 V
Height	182.9 cm
Width	5.6 cm
Output Voltage	230 V
Depth	5.1 cm
Net Weight	6.76 kg
Mounting Location	Side
Mounting Preference	No preference
Input Plug Type	IEC 60309 16 A 2P + E
Mounting Mode	Rack-mounted
Rack Units	0U
Mounting Position	Vertical
Permissible Voltage	100240 V

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Input Current Limits	16 A
Load Capacity	3700 VA
Network Frequency	50/60 Hz
Total Number Of Outlets	21 IEC 60320 C13 3 IEC 60320 C19

Environment

Product Certifications	UL listed VCCI class A VDE
Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC part 15 class A ICES-003
Ambient Air Temperature For Operation	-560 °C
Relative Humidity	595 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2565 °C
Storage Relative Humidity	595 %
Storage Altitude	0.0015240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	203.7 cm
Package 1 Width	16.3 cm
Package 1 Length	11.7 cm
Package 1 Weight	9.03 kg

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Lead Free

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation

Eu Rohs Directive

Compliant with Exemptions

Environmental Disclosure

Product Environmental Profile

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

End of Life Information