Specifications



APC NetShelter SX, Server Rack Enclosure, 48U, Grey, 2258H x 600W x 1070D mm

AR3107G

() Discontinued on: 13 Sept 2021

| Overview | | | | | |
|---------------------------|---|--|--|--|--|
| Presentation | Tall enclosure with 48U spaces for additional equipment. Compact width to optimize data center space. For low to medium density server and networking applications. | | | | |
| Lead Time | Usually in Stock | | | | |
| Main | | | | | |
| Product Or Component Type | Rack enclosure | | | | |
| Number Of Rack Unit | 48U | | | | |
| Provided Equipment | Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels | | | | |

Physical

| <i>.</i> | | |
|----------------------------|---|--|
| Height | 225.8 cm | |
| Width | 60 cm | |
| Depth | 107 cm | |
| Net Weight | 138.23 kg | |
| Colour | Grey | |
| Mounting Preference | No preference | |
| Mounting Mode | Not rack-mountable | |
| Maximum Mounting Depth | 91.49 cm | |
| Minimum Mounting Depth | 19.1 cm | |
| Rack Width | 19" | |
| Marking | 14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels | |
| Permanent Permissible Load | 1020.58 kg dynamic 1700.97 kg static | |

Conformance

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 238.5 cm |
| Package 1 Width | 75.2 cm |
| Package 1 Length | 121.9 cm |
| Package 1 Weight | 157.349 kg |

Contractual warranty

Warranty

5 year repair or replace

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Take-back Transparency RoHS/REACh

Resource performance

Take-Back Program Available

Well-being performance

| 🕑 Re | ach Free Of Svhc | | |
|-------|--------------------------|-----|--|
| 🕑 To: | xic Heavy Metal Free | | |
| 🕑 Me | rcury Free | | |
| 🕑 Ro | hs Exemption Information | Yes | |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |