





APC NetShelter SX, Server Rack Enclosure, 48U, without Sides and Doors, Black, 2258H x 600W x 1200D mm

AR3307X617

Overview

Presentation	Deep and Tall Universal IT Enclosure for low to medium density server and networking applications that either require additional equipment clearance space or more open space for ease of access in the rear of the enclosure. Tall to provide 48U spaces for environments that can take advantage of higher spaces and provide more mounting u-spaces at each enclosure footprint. Compact width to optimize data center space.
Lead Time	Usually in Stock

Main

Product Or Component Type	Rack enclosure
Number Of Rack Unit	48U
Provided Equipment	Baying hardware Key(s) Leveling feet Mounting hardware Pre-installed casters

Physical

Height	225.8 cm
Width	60 cm
Depth	120 cm
Net Weight	149.55 kg
Colour	Black
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	105.99 cm
Minimum Mounting Depth	19.1 cm
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge post 18 gauge roof
Permanent Permissible Load	1020.58 kg dynamic 1360.78 kg static

Conformance

Standards	UL 2416
	UL 60950-1
	EIA-310E

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	238.5 cm
Package 1 Width	133.4 cm
Package 1 Length	74.6 cm
Package 1 Weight	165.45 kg

Contractual warranty

Warranty 5 year repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance

✓ Reach Free Of Svhc
 ✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile