



## Overview

Presentation	Netshelter CX Mini is specifically designed to house a complete small-office IT installation comprised of one or two servers, network hardware and peripheral devices. It combines extreme noise reduction and moderate thermal capacity with exceptional reliability and an all-inclusive, plug-and-play specification. Designed to accept tower form factor servers, the CX Mini can also be converted to accept rack form factor servers using a 12U rack mount conversion kit (AR4000MV12U). The resulting EIA rack is 600 mm/23.6" deep. NAM power cords sold separately, part number AR4605.
Lead time	Special Order - Call for Quoted Lead Times

## General

Provided equipment	<ul style="list-style-type: none"> <li>Brush strips</li> <li>Door</li> <li>Key(s)</li> <li>Lockable door</li> <li>Office-type casters</li> <li>Power strip with (3) IEC receptacles</li> <li>Fans</li> <li>Removeable lockable rear panel</li> <li>Soundproofing</li> <li>Unpacking sheet</li> </ul>
--------------------	--

## Physical

Cable length	0.61 m
Maximum mounting depth	70 cm
Colour	White
Depth	93 cm
Height	72 cm
Net weight	75 kg
Width	69 cm

## Input

Network frequency	50/60 Hz
-------------------	----------

Plug standard	NEMA 5-15P IEC 60320 C14
Input voltage	100 V 120 V 200 V 208 V 220 V 230 V 240 V

## Conformance

Product certifications	TAA compliance
------------------------	----------------

## Packing Units

Package 1 Weight	80 kg
Package 1 Height	75 cm
Package 1 width	74 cm
Package 1 Length	98 cm
Number of Units in Package 3	1

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	2 year (manufacturer's defect)
----------	--------------------------------