

Product datasheet

Specifications



APC NetShelter CX, 38U,
Soundproof Server Rack
Enclosure, 200V to 240V, Dark
Grey, 1950H x 750W x 1130D mm

AR4038IX431

! Discontinued

! Discontinued on: 23 May 2023

Overview

Presentation	Specialized enclosures with integrated cooling, noise dampening, and power distribution for server and network applications in office environments.
Lead Time	Special Order - Call for Quoted Lead Times

Main

Product Or Component Type	Rack enclosure
Main Input Voltage	200 V 208 V 220 V 230 V 240 V
Main Output Voltage	200 V 240 V
Input Connection Type	IEC 60320 C14
Output Connection Type	12 IEC 60320 C13
Number Of Rack Unit	38U
Provided Equipment	Casters Installation guide Key(s) Leveling feet Rack power distribution unit (PDU) Side panels

Physical

Height	195 cm
Width	75 cm
Depth	113 cm
Net Weight	202.5 kg
Colour	Grey
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	88.01 cm
Minimum Mounting Depth	72.01 cm
Rack Width	19"
Permanent Permissible Load	778.36 kg static

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Input

Network Frequency	50/60 Hz
-------------------	----------

Conformance

Product Certifications	TAA compliance
Standards	EIA-310D

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	215 cm
Package 1 Width	120 cm
Package 1 Length	80 cm
Package 1 Weight	230 kg

Contractual warranty

Warranty	2 year (manufacturer's defect)
----------	--------------------------------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)




Take-back Transparency RoHS/REACH

Resource performance


 Take-Back Program Available

Well-being performance

 Reach Free Of Svhc

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)
[EU RoHS Declaration](#)

Environmental Disclosure [Product Environmental Profile](#)