## **Product datasheet**

Specifications





# VarPlus Can HDuty Capacitor - 25/30 kvar - 440 V - 50/60Hz

BLRCH250A300B44

#### Price: 2,694.27 ZAR

#### Main

Range Of Product	PowerLogic	
Product Or Component Type	Heavy duty capacitor	
Network Frequency	50/60 Hz	
Series Name	HDuty	
Network Harmonic Content	<= 20 %	
Electrical Parameters	25 kvar 440 V 50 Hz 30 kvar 440 V 60 Hz	
Maximum Permissible Voltage	1.1 x Un (8 hours over 24 hours)	
Continuous Overcurrent Capacity	y 1.8 x ln	
Rated Voltage	440 V AC 50/60 Hz	

#### Complementary

Dielectric Losses	< 0.2 W/kvar	
Power Losses	< 0.5 W/kVAr	
Capacitance Tolerance	- 5 % to 10 %	
Voltage Test	2.15 x Un AC between terminals for 10 s <= 660 V - 3 kV AC between terminal and container for 10 s >= 660 V - 6 kV AC between terminal and container for 10 s	
Inrush Current	h Current 250 x In	
Maximum Switching Operation Per Year		
Service Life In Hours	130000 h	
Dielectric Material	Metallized polypropylene film with Zn/Al alloy, special resistivity & profile, special edge (wave cut)	
Impregnation Material	Non-PCB dry PUR resin Biodegradable	
Type Of Installation	Indoor installation	
Connections - Terminals	ClampTite terminal	
Mounting Mode	Upright/horizontal	
Diameter	e <b>r</b> 116 mm	
Height	242 mm	
Net Weight 2.5 kg		

### Environment

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Standards	IEC 60831-1 IEC 60831-2	
Ip Degree Of Protection	IP20	
Operating Altitude	2000 m	
Temperature Class	D	
Ambient Air Temperature For Operation	-2555 °C	
Relative Humidity	95 %	

## **Packing Units**

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19 cm
Package 1 Width	20 cm
Package 1 Length	33 cm
Package 1 Weight	3.015 kg
Unit Type Of Package 2	S06
Number Of Units In Package 2	15
Package 2 Height	74 cm
Package 2 Width	60 cm
Package 2 Length	80 cm
Package 2 Weight	45.225 kg
Unit Type Of Package 3	S06
Number Of Units In Package 3	15
Package 3 Height	74 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	45.225 kg

#### **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins