

Product datasheet

Specifications



Global socket with shutter, ZENcolo, 16A, 1 gang, Silver bronze

E84426_16IS_SZ

Price* : 212.45 ZAR

Main

Range	ZENcolo
Product or component type	Power socket-outlet
Socket additional information	Shuttered
Outlet poles configuration	2P + E universal
Load type	Resistive
Cover frame colour tint	Silver bronze

Complementary

Device mounting	Flush Surface
Rated current	16 A at 250 V AC 50/60 Hz
Number of gangs	1 gang
Material	Polycarbonate base Polycarbonate grid plate Polycarbonate surround Brass metal parts Phosphor bronze metal parts
Connections - terminals	Folded terminal without pressure plate
Embedding depth	18.95 mm
Width	87 mm
Height	87 mm
Depth	29 mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	IEC 60884-1 IEC 60884-1

* Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.0 cm
Package 1 Width	32.5 cm
Package 1 Length	50.0 cm
Package 1 Weight	139.125 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Recommended replacement(s)