

G55TE-BB40K30

MGE Galaxy 5500 E Backup Time Blocks & C Breaker 40kVA 30mn Off Shore & Marine



Overview

Description	This kit includes battery blocks, circuit breaker, cabling and temperature sensor. The cabinets are not included in that sku. The sku for marine battery cabinet is called G55TE-ECxxK30 composed of Empty Battery Cabinet.
Model Name	MGE Galaxy 5500 E Backup Time Blocks & C Breaker 40kVA 30mn Off Shore & Marine
Includes	User Manual
Standard Lead Time	Special Order - Call for Quoted Lead Times
Product Distribution	Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Austria , Azerbaijan , Bahamas , Bahrain , Barbados , Belarus , Belgium , Belize , Benin , Bermuda , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Bulgaria , Burkina Faso , Burundi , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , Chile , Colombia , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Costa Rica , Cote D'Ivoire , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominica , Dominican Republic , Ecuador , Egypt , El Salvador , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Falkland Islands (Malvinas) , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Grenada , Guadeloupe , Guatemala , Guinea , Guyana , French Guiana , Haiti , Honduras , Hungary , Iceland , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Jordan , Kazakhstan , Kenya , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Mali , Malta , Martinique , Mauritania , Mauritius , Mayotte , Mexico , Moldova , Republic Of , Mongolia , Morocco , Mozambique , Namibia , Netherlands , Netherlands Antilles , Nicaragua , Niger , Nigeria , Norway , Oman , Pakistan , Panama , Paraguay , Peru , Poland , Portugal , Puerto Rico , Qatar , Reunion , Romania , Russian Federation , Rwanda , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Saudi Arabia , Senegal , Sierra Leone , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sudan , Suriname , Sweden , Switzerland , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Togo , Trinidad And Tobago , Tunisia , Turkey , Turkmenistan , Turks And Caicos Islands , Uganda , Ukraine , United Arab Emirates , United States , Uruguay , Uzbekistan , Venezuela , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe

Batteries & Runtime

Battery Volt-Amp-Hour Capacity	0
Battery Type	VRLA
Battery mounting	--
Included Battery Modules	0
Battery Slots Empty	0

Physical

Net Weight	1218.0 kg
Maximum Height	850.0 mm

Maximum Width	2000.0 mm
Maximum Depth	800.0 mm
Shipping Weight	1243.0 kg
Shipping Width	2000.0 mm
Shipping Height	1000.0 mm
Shipping Depth	800.0 mm
Rack Height	0 U
Units per Pallet	0.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-999,9 meters
Storage Temperature	-20 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-3600 meters

Conformance

Approvals	CE
Standard warranty	1 year repair or replace