

G55TTC40RH

MGE Galaxy 5500 Transformer 20 to 40 kVA in a stand alone cabinet



Purchase

APC
[G55TTC40RH](#)

Overview

Description	Three phase transformer for a 20 or 40kVA UPS in a stand alone cabinet
Model Name	MGE Galaxy 5500 Transformer 20 to 40 kVA in a stand alone cabinet
Includes	Installation guide , User Manual
Standard Lead Time	Usually Ships within 3 Weeks
Product Distribution	Andorra , United Arab Emirates , Afghanistan , Antigua And Barbuda , Anguilla , Albania , Armenia , Netherlands Antilles , Angola , Argentina , Austria , Australia , Aruba , Azerbaijan , Bosnia And Herzegovina , Barbados , Bangladesh , Belgium , Burkina Faso , Bulgaria , Bahrain , Burundi , Benin , Bermuda , Brunei Darussalam , Bolivia , Brazil , Bahamas , Bhutan , Botswana , Belarus , Belize , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Central African Republic , Congo , Switzerland , Cote D'Ivoire , Cook Islands , Chile , Cameroon , China , Colombia , Costa Rica , Serbia And Montenegro , Cuba , Cyprus , Czech Republic , Germany , Djibouti , Denmark , Dominica , Dominican Republic , Algeria , Ecuador , Estonia , Egypt , Western Sahara , Spain , Ethiopia , Finland , Fiji , Falkland Islands (Malvinas) , France , Gabon , United Kingdom , Grenada , Georgia , French Guiana , Ghana , Gibraltar , Gambia , Guinea , Guadeloupe , Equatorial Guinea , Greece , Guatemala , Guyana , Hong Kong , Honduras , Croatia , Haiti , Hungary , Indonesia , Ireland , Israel , India , Iraq , Iran (Islamic Republic Of) , Iceland , Italy , Jamaica , Jordan , Japan , Kenya , Cambodia , SAINT KITTS AND NEVIS , KOREA, REPUBLIC OF , Kuwait , Cayman Islands , Kazakhstan , Lebanon , SAINT LUCIA , Liechtenstein , Sri Lanka , Liberia , Lesotho , Lithuania , Luxembourg , Latvia , Morocco , Moldova, Republic Of , Madagascar , Macedonia , Mali , Myanmar , Martinique , Mauritania , Malta , Mauritius , Malawi , Mexico , Malaysia , Mozambique , Namibia , Niger , Nigeria , Nicaragua , Netherlands , Norway , Nepal , New Zealand , Oman , Panama , Peru , Papua New Guinea , Philippines , Pakistan , Poland , Puerto Rico , Portugal , Paraguay , Qatar , Reunion , Romania , Russian Federation , Rwanda , Saudi Arabia , Sudan , Sweden , Singapore , Slovenia , Slovakia (Slovak Republic) , Sierra Leone , Senegal , Somalia , El Salvador , Turks And Caicos Islands , Chad , Togo , Thailand , Turkmenistan , Tunisia , East Timor , Turkey , Trinidad And Tobago , Taiwan , TANZANIA, UNITED REPUBLIC OF , Ukraine , Uganda , Uruguay , Uzbekistan , SAINT VINCENT AND THE GRENADINES , Venezuela , VIRGIN ISLANDS (UNITED STATES) , Viet Nam , Yemen , Mayotte , South Africa , Zambia , Zimbabwe

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Output

Nominal Output Voltage	400V 3PH
Output Connections	(1) Hard Wire 5-wire (3PH + N + G) (Battery Backup)

Input

Nominal Input Voltage	400V 3PH
-----------------------	----------

Physical

Net Weight	270 kg
Maximum Height	1900 mm
Maximum Width	400 mm
Maximum Depth	848 mm
Shipping Weight	360 kg
Shipping Height	2230 mm
Shipping Width	790 mm
Shipping Depth	1010 mm

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-999.9 meters
Storage Temperature	-20 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-9000 meters

Conformance

Standard warranty	1 year on-site repair or replace with factory authorized Start-Up
-------------------	---