# **Product datasheet**

Specification





TeSys D - contactor coil - LXD1 - 32 V AC 50/60 Hz for 9... 38 A contactor

LXD1C7

Price: 710.85 ZAR

## Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LXD1
Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	32 V AC 50/60 Hz
Average Resistance	10.1 Ohm at 20 °C
Inductance Of Closed Circuit	0.39 H
Product Compatibility	LC1D09D38 LC1DT20DT40 CAD
Mechanical Durability	15 Mcycles
Maximum Operating Rate	3600 cyc/h 60 °C

## Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Drop-out: 0.30.6 Uc at 50/60 Hz (at <60 °C) Operational: 0.81.1 Uc at 50 Hz (at <60 °C) Operational: 0.851.1 Uc at 60 Hz (at <60 °C)
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 20 °C) 70 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 20 °C) 7 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	23 W at 50/60 Hz

## **Environment**

Ambient Air Temperature For Operation	-560 °C
Net Weight	0.07 kg

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	6.2 cm
Package 1 Length	4.0 cm
Package 1 Weight	67.0 g

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

## **Contractual warranty**

Warranty

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>②</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information Yes	
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information