Product datasheet

Specification





TeSys D - contactor coil - LXD1 - 220 V AC 50/60 Hz for 9... 38 A contactor

LXD1M7

Price: 710.85 ZAR

Main

Range	TeSys	
Product Or Component Type	Contactor coil	
Device Short Name	LXD1	
Control Circuit Type	AC at 50/60 Hz	
[Uc] Control Circuit Voltage	220 V AC 50/60 Hz	
Average Resistance	515.4 Ohm at 20 °C	
Inductance Of Closed Circuit	18 H	
Product Compatibility	CAD LC1D09D38 LC1DT20DT40	
Mechanical Durability	15 Mcycles	
Maximum Operating Rate	3600 cyc/h 60 °C	

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Drop-out: 0.30.6 Uc at 50/60 Hz (at <60 °C) Operational: 0.81.1 Uc at 50 Hz (at <60 °C) Operational: 0.851.1 Uc at 60 Hz (at <60 °C)
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 20 °C) 70 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 20 °C) 7 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	23 W at 50/60 Hz

Environment

Ambient Air Temperature For Operation	-560 °C
Net Weight	0.07 ka

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	6.300 cm
Package 1 Length	4.000 cm
Package 1 Weight	67.000 g

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Unit Type Of Package 2	S02
Number Of Units In Package 2	100
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	7.134 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information