Product datasheet

Specification





U.motion KNX Server Plus, Touch 10

MTN6260-0410

! Discontinued on: 23 Jul 2021

① To be discontinued

Main

Range Of Product	U.motion	
Range Compatibility	KNX	
Product Or Component Type	Server + touch panel	
Device Short Name	Touch 10	
Product Destination	U.motion system KNX bus system	
Product Compatibility	U.motion touch panel Client Touch 7 smartphone tablet PC	
Bus Type	KNX Ethernet	
Operating System	Linux	
Display Size	10.1 inch	
Display Colour	65000 colours	
Colour Tint	Aluminium	

Complementary

Connector Type	1 RJ45	
	4 USB	
Integrated Connection Type	Loudspeaker	
	Microphone	
Device Mounting	Flush	
[Ue] Rated Operational Voltage	100240 V AC	
Maximum Power Consumption In W	20 W operation	
Control Type	Touch screen	
Display Type	TFT	
Display Resolution	1024 x 600 pixels WSVGA	
Illuminating Intensity	200 cd	
Function Available	Visualisation	
Memory Type	1 GB DDR2 SDRAM	
Mounting Position	Horizontal	
Material	Plastic and metal	
Height	343 mm	

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Width	201 mm
Depth	81 mm
Net Weight	2.2 ka

Environment

Ambient Air Temperature For Operation	030 °C
Ip Degree Of Protection	IP20 conforming to EN 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	36 cm
Package 1 Width	26.5 cm
Package 1 Length	51 cm
Package 1 Weight	4 ka



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

⊘	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)