# **Product datasheet**

Specifications





# Spacial CRN plain door w/o mount.plate. H1000xW800xD250 IP66 IK10 RAL7035..

NSYCRN108250

#### Price: 5,686.90 ZAR

#### Main

| Range                       | Spacial   |
|-----------------------------|---|
| Product Name                | Spacial CRN   |
| Application                 | Multi-purpose   |
| Category                    | Compact enclosure   |
| Enclosure Nominal Height    | 1000 mm   |
| Enclosure Nominal Width     | 800 mm  |
| Enclosure Nominal Depth     | 250 mm  |
| Installation Accessory Type | Wall-mounting   |
| Device Composition          | 1 body<br>1 door<br>1 lock<br>2 cable gland plate: bottom |
| Door Type                   | Plain   |
| Mounting Plate Description  | Without mounting plate                                    |

#### Complementary

| Body Type                   | Back welded with double profile forming a protected sealed area<br>Sides made from a single folded section |
|-----------------------------|--|
| Number Of Doors             | Front face: 1 door(s)  |
| Door Opening Side           | Reversible (120 °)   |
| Lock Type                   | 3 mm double-bar lock   |
| Type Of Gland Plate         | Standard   |
| Accessibility For Operation | Front  |
| Removable Parts             | Door by hinges<br>Cable gland plate by screws  |
| Material                    | Body: steel  |
| Surface Finish              | Epoxy-polyester powder   |
| Colour                      | Grey (RAL 7035)  |
| Standards                   | IEC 62208  |
| Product Certifications      | UL<br>cUL<br>DNV-GL  |
| Net Weight                  | 33 kg  |

### Environment

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

| Ip Degree Of Protection | IP66 conforming to IEC 60529 |
|-------------------------|------------------------------|
| Ik Degree Of Protection | IK10 conforming to IEC 62262 |

# **Packing Units**

| Unit Type Of Package 1       | PCE        |
|------------------------------|------------|
| Number Of Units In Package 1 | 1          |
| Package 1 Height             | 27.0 cm    |
| Package 1 Width              | 81.0 cm    |
| Package 1 Length             | 101.5 cm   |
| Package 1 Weight             | 28.466 kg  |
| Unit Type Of Package 2       | PAM        |
| Number Of Units In Package 2 | 8          |
| Package 2 Height             | 175.0 cm   |
| Package 2 Width              | 100.0 cm   |
| Package 2 Length             | 120.0 cm   |
| Package 2 Weight             | 240.728 kg |

# **Contractual warranty**

Warranty

18 months

### Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation    | China RoHS declaration<br>Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |