Product datasheet

Specification





Floor standing enclosure polyester vers.PLA completely sealed 500x500x420 IP65

NSYPLA554G

Price: 11,056.62 ZAR

Main

| Thalassa |
|--|
| Thalassa PLA |
| Multi-purpose |
| Suitable enclosure |
| PLA |
| 500 mm |
| 500 mm |
| 420 mm |
| Floor-standing |
| 1 top part 1 bottom part 2 side part 1 rear panel 1 door |
| |

Complementary

| Body Type | Sealed top and bottom part assembled with side parts |
|-----------------------------|---|
| Door Type | Plain front |
| Number Of Doors | 1 door(s) |
| Door Opening Side | Reversible (120 °) |
| Lock Type | 2 points lock, 5 mm double-bar |
| Accessibility For Operation | Rear Front |
| Removable Parts | Door by hinges Rear panel by fixing element |
| Material | Polyester reinforced with fibreglass |
| Colour | Grey (RAL 7035) |
| Standards | IEC 62208 UL 508 A |
| Nema Degree Of Protection | NEMA 5 NEMA 12 NEMA 13 NEMA 3S NEMA 2 NEMA 3X NEMA 3X NEMA 3R NEMA 3 NEMA 3 |

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"



| Product Certifications | DNV Marine Veritas UL/cUL listed |
|-----------------------------|--|
| Electrical Insulation Class | Class II |

Environment

| Ip Degree Of Protection | IP65 conforming to IEC 60529 (completely sealed) |
|-------------------------------------|--|
| Ik Degree Of Protection | IK10 conforming to IEC 62262 (plain door) |
| Fire Resistance | 960 °C conforming to IEC 62208 |
| Ambient Air Temperature For Storage | -3590 °C |

Packing Units

| _ | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 51.0 cm |
| Package 1 Width | 54.0 cm |
| Package 1 Length | 48.0 cm |
| Package 1 Weight | 16.02 kg |
| Unit Type Of Package 2 | PAM |
| Number Of Units In Package 2 | 12 |
| Package 2 Height | 120 cm |
| Package 2 Width | 100 cm |
| Package 2 Length | 167 cm |
| Package 2 Weight | 191 kg |



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |