# **Product datasheet**

Specifications





Spacial S3D plain door w/o mount.plate. H1000xW600xD250 IP66 IK10 RAL7035.

NSYS3D10625

### Price: 6,444.01 ZAR

#### Main

Range	Spacial
Product Name	Spacial S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	1000 mm
Enclosure Nominal Width	600 mm
Enclosure Nominal Depth	250 mm
Door Type	Plain
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Standard
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 door 1 lock 1 cable gland plate

### Complementary

Body Type	Single piece body Gutter-shaped front rail double sheet thickness
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, 3 mm double-bar
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws
Material	Steel
Surface Finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	BV GL UL cUL DNV LR
Net Weight	28 kg

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

### Environment

Nema Degree Of Protection	NEMA 4X/13
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ip Degree Of Protection	IP66 conforming to IEC 60529

# **Packing Units**

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.5 cm
Package 1 Width	62.5 cm
Package 1 Length	103.0 cm
Package 1 Weight	24.8 kg
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	9
Package 2 Height	200.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	252.0 kg

# **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations