Product datasheet

Specifications





SPACIAL S3X stainless 304L, Scotch Brite® finish, H1200xW1000xD300 mm.

NSYS3X121030

Price: 39,985.97 ZAR

Main

Range	Spacial
Product Name	Spacial S3X
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	1200 mm
Nominal Width	1000 mm
Nominal Depth	300 mm
Product Installation	Wall-mounting
Device Composition	1 body 2 door 1 lock: door 1 reinforcement frame drilled: door

Complementary

Body Type	Single piece body, cross-shaped structure Gutter shaped front rail
Door Type	Plain
Number Of Doors	Front face: 2 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, 3 mm double-bar
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body and door: stainless steel 304L Hinge: stainless steel
Surface Finish	Body and door: Scotch-Brite® brushed
Net Weight	51.8 kg

Environment

Standards	IEC 62208
Product Certifications	CAN/CSA 22 UL 508 type A
Ip Degree Of Protection	IP55 conforming to IEC 60529

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Ik Degree Of Protection	IK10 conforming to IEC 62262
Environmental Characteristic	Specific hygiene
	Corrosive

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	121.92 cm
Package 1 Width	30.48 cm
Package 1 Length	101.6 cm
Package 1 Weight	34.02 kg
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	3
Package 2 Height	122 cm
Package 2 Width	100 cm
Package 2 Length	117 cm
Package 2 Weight	180 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations