



Main

| | |
|----------------------|---|
| Range | Spacial |
| Product name | Spacial S3X |
| Enclosure type | Multi-purpose |
| Category | Compact enclosure |
| Nominal height | 600 mm |
| Nominal width | 400 mm |
| Nominal depth | 200 mm |
| Product installation | Wall-mounting |
| Device composition | 2 lock (door) 1 body 1 door 2 perforated vertical profile drilled (door) |

Complementary

| | |
|-----------------------------|---|
| Body type | Single piece body, cross-shaped structure Gutter shaped front rail |
| Door type | Plain |
| Number of doors | Front face : 1 door(s) |
| Door opening side | 120 °, reversible |
| Lock type | 2 points lock, 3 mm double-bar |
| Mounting plate description | Without mounting plate |
| Type of gland plate | Without gland plate |
| Accessibility for operation | Front |
| Removable parts | Door fixing: by hinges |
| Material | Lock : zamak Hinge : stainless steel Body and door : stainless steel 316L |
| Surface finish | Lock : chromium plated Body and door : Scotch-Brite® brushed |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|----------------|---------|
| Thickness | 1.5 mm |
| Product weight | 9.52 kg |

Environment

| | |
|------------------------------|-------------------------------|
| Standards | IEC 62208 |
| Product certifications | CAN/CSA 22 UL 508 type A |
| IP degree of protection | IP66 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |
| Environmental characteristic | Corrosive Specific hygiene |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0810 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available Product Environmental Profile |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|---------------------|
| Warranty period | 18 months 18 months |
|-----------------|---------------------|