Product datasheet

Specifications





set of 4 Spacial SF lifting bracket zinc coated steel

NSYSFELB

Price: 886.07 ZAR

Main

Area	Spacial
Category	Lifting accessory
Product Or Component Type	Lifting bracket
Application	Multi-purpose
Mounting Location	Enclosure top
Mounting Support	Directly in the axis of the uprights
Range Compatibility	Spacial Spacial SF Spacial Spacial SFHD Spacial Spacial SFM
Device Composition	4 bracket fixing elements
Quantity Per Set	Set of 1

Complementary

Material	Steel
Surface Finish	Zinc coated
Fixing Mode	By screws - screw type M12
Permanent Permissible Load	500 kg
Height	60 mm
Width	100 mm
Depth	49 mm
Diameter	32 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	9.000 cm
Package 1 Length	15.000 cm
Package 1 Weight	1.930 kg
Unit Type Of Package 2	S02
Number Of Units In Package 2	6
Package 2 Height	15.000 cm

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	11.840 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	96
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	201.440 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations