Product datasheet





Spacial SFHF - electromagnetic protected enclosure - H=1800 x W=800 x D=400 mm

NSYSFHF18840

! Discontinued on: 01 Nov 2020

(!) Discontinued

Price: 86,808.07 ZAR

Main

Range	Spacial
Extended Range	Spacial SFHF
Product Or Component Type	Suitable enclosure
Enclosure Type	Electromagnetic protected
Enclosure Nominal Height	1800 mm
Enclosure Nominal Width	800 mm
Enclosure Nominal Depth	400 mm
Enclosure Mounting	Floor-standing
Device Composition	2 sliding rails 4 mounting plate bracket 1 structure 1 door 1 locking system with handle: door 1 rear panel 1 roof 4 adaptor upright

Complementary

Structure Type	Panels and doors built into the structure Vertical uprights joined with top and bottom frames Formed from a single section Perforated structure with a pitch of 25 mm
Door Type	Plain front
Number Of Doors	Front: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	4 points lock, handle with 5 mm double bar insert front door
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Sides of enclosure Front Rear
Removable Parts	Door by screws hinge Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"



Material	Frame: galvanised steel Uprights: galvanised steel Hinge: zamak Handle: polyamide 6 with 30 % fibre glass Panels: aluzinc Door: aluzinc
Surface Finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)

Environment

Standards	EMC/EN/IEC 61547 IEC 62208
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations