

# Product datasheet

Specifications



## Spacial SFHF - electromagnetic protected enclosure - H=2000 x W=800 x D=400 mm

NSYSFHF20840

 **Discontinued on:** 01 Nov 2020

 **Discontinued**

**Price: 88,647.76 ZAR**

### Main

Range	Spacial
Extended Range	Spacial SFHF
Product Or Component Type	Suitable enclosure
Enclosure Type	Electromagnetic protected
Enclosure Nominal Height	2000 mm
Enclosure Nominal Width	800 mm
Enclosure Nominal Depth	400 mm
Enclosure Mounting	Floor-standing
Device Composition	2 sliding rails 4 mounting plate bracket 1 structure 1 door 1 locking system with handle: door 1 rear panel 1 roof 4 adaptor upright

### Complementary

Structure Type	Formed from a single section Perforated structure with a pitch of 25 mm Panels and doors built into the structure Vertical uprights joined with top and bottom frames
Door Type	Plain front
Number Of Doors	Front: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	4 points lock, handle with 5 mm double bar insert front door
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Sides of enclosure Rear Front
Removable Parts	Door by screws hinge Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Material	Frame: galvanised steel Uprights: galvanised steel Hinge: zamak Handle: polyamide 6 with 30 % fibre glass Panels: aluzinc Door: aluzinc
Surface Finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)

## Environment

Standards	IEC 62208 EMC/EN/IEC 61547
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262