

Product datasheet

Specifications



CANopen SUB-D9 female connector - bended at 90° w additional SUB-D9 - IP20

TSXCANKCDF90TP

Price: 2,038.14 ZAR

Main

Range Of Product	CANopen
Bus Type	CANopen
Accessory / Separate Part Category	Connection accessories
Accessory / Separate Part Type	Connector with line terminator
Ip Degree Of Protection	IP20
Accessory / Separate Part Destination	CANopen bus

Complementary

Electrical Connection	1 female connector SUB-D 9 elbowed 1 male connector SUB-D 9
Net Weight	0.051 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.600 cm
Package 1 Width	10.500 cm
Package 1 Length	14.900 cm
Package 1 Weight	51.000 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	225
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	11.475 kg

Contractual warranty

Warranty	18 months
----------	-----------

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation		China RoHS declaration