Product datasheet

Specifications





Actassi S-110 Connector RJ45 Keystone Unshielded Cat 6 Shuttered White bag x 1

VDIB17746UWE

() Discontinued on: 23 Jan 2021

① Discontinued

Main

| Range | Actassi |
|-----------------------------|---|
| Product Type | RJ45 network socket |
| Device Presentation | Integrated shutter Two piece design |
| Colour Tint | Stuffer cap: transparent (ABS + PC) IDC cover: blue (ABS + PC) Connector housing: white (ABS + PC) Shutter: white (ABS + PC) |
| Wiring Colour Configuration | 568 A/B |
| Quantity Per Set | Set of 1 |

Complementary

| 1.5 A at 25 °C |
|--|
| 1000 V AC/DC peak, between contacts |
| 20 mOhm |
| Initial insulation resistance: >= 500 MOhm at 100 V DC |
| AWG 24AWG 23 |
| 750 cycles |
| >= 35 dB at 30100 MHz >= 75 - 20 x log(f) dB at 1001000 MHz |
| 8 pins of copper alloy and gold plated conforming to IEC 60603-7 |
| 50 N during 60 s |
| >= 50 dB >= 68 - 20 x log(f) dB at 1250000 kHz |
| Punch down tool Quick termination tool |
| 0.91.1 mm |
| UTP |
| 6 |
| 1000BASE-T |
| PoE+ (Power over Ethernet) VoIP (Voice IP) |
| RJ45 plug |
| 0250 MHz |
| |

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

| Type Of Footprint | S-110 keystone |
|-------------------|-------------------------|
| Height | 22 mm |
| Length | 36 mm |
| Width | 16 mm |
| Targeted Region | Europe Asia Pacific. |

Environment

| Operational Temperature Range | -4070 °C |
|-------------------------------|---------------------------------|
| Climatic Category | 40/070/21 (21 days) |
| Flame Retardance | UL94-V0 conforming to UL listed |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3 cm |
| Package 1 Width | 3 cm |
| Package 1 Length | 2 cm |
| Package 1 Weight | 0.008 kg |

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

| Toxic Heavy Metal Free | |
|----------------------------|-----|
| Mercury Free | |
| Rohs Exemption Information | Yes |

Certifications & Standards

| Eu Rohs Directive | Compliant |
|--------------------------|---|
| | EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| | Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |