Product datasheet

Specification





Harmony XVL. Pilot light. plastic. green. Ø12. covered LED. 24 V DC

XVLA333

Price: 364.68 ZAR

Main

Range Of Product	Harmony XVL				
Product Or Component Type	ype LED pilot light with integral lens cap				
Component Name	XVL				
Mounting Diameter	12 mm				
Light Source	Covered LED				
Light Block Colour	Green				
Protection Type	Integral ballast resistor Built-in by diode				
[Us] Rated Supply Voltage	24 V				
Ip Degree Of Protection	Degree Of Protection IP65 (with seal XVLZ912) conforming to IEC 60529 IP65 (with seal XVLZ912) conforming to NF C 20-010 IP40 conforming to IEC 60529 IP40 conforming to NF C 20-010				

Complementary

Supply Circuit Type	DC		
Connections - Terminals	Threaded connector: clamping capacity 1 x 0.21 x 1.5 mm²		
Current Consumption	18 mA		
[Ui] Rated Insulation Voltage	50 V conforming to IEC 60947-1		
Bulb Lifespan	100000 h		
Nominal Voltage Limit	0.81.1 Un		
Terminals Description Iso N°1	(X1-X2)PL		
Height	16 mm		
Width	16 mm		
Depth	51 mm		
Net Weight	0.007 kg		

Environment

Product Certifications	CSA UL
Protective Treatment	тс
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4070 °C

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Overvoltage Category	Class 3 conforming to IEC 60536
	Class 3 conforming to NF C 20-030

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.6 cm
Package 1 Width	1.6 cm
Package 1 Length	4.9 cm
Package 1 Weight	7.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3.0 cm
Package 2 Width	9.0 cm
Package 2 Length	16.0 cm
Package 2 Weight	73.0 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	951.0 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

XVLA333

Dimensions Drawings

LED Pilot Light

Dimensions




- (1) Threaded connector
- e panel thickness: 1 to 8 mm/0.03 to 0.31 in.

XVLA333

Mounting and Clearance

LED Pilot Light

Panel Drilling



Ø min		G min		H min	
mm	in.	mm	in.	mm	in.
12.2	0.48	16.5	0.65	16.5	0.65