Product datasheet

Specifications

Green Premium™

Vivace 10A 250V BELL PRESS Switched,Aluminium silver

KB31BPB_AS_G2

Main

Range	Vivace
Product Or Component Type	Bell press switch
Device Short Name	KB31
Device Application	Control
Additional Switch Application	Bell switch
Switch Function	1-way

Complementary

Device Presentation	Complete mechanism
Actuator	Rocker
Number Of Gangs	1 gang
Colour Tint	Aluminium silver
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting Depth	8 mm
Device Mounting	Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Fixing Center	60.3 mm
Embedding Depth	35 mm
Rated Current	10 A at 250 V AC, inductive
[Ue] Rated Operational Voltage	250 V AC
Network Frequency	50 Hz
Contacts Material	Brass and phosphor bronze
Connections - Terminals	pillar terminal
Terminal Identifier	L1 L2 COM
Tightening Torque	0.4 N.m
Clamping Connection Capacity	1.5 mm²
Width	87 mm
Height	87 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	SS 227 MS IEC 60669-1 IEC 60669-1
Ambient Air Temperature For Operation	-5…40 °C
Relative Humidity	0…95 %
Environmental Characteristic	Indoor use

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO_2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >

Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations