

# Product datasheet

Specifications



## 10A 2 Pin Switched Socket Outlet, Grey Silver

E3015US\_GS

! Discontinued on: 20 Jun 2023

! Discontinued

### Main

Range	Neo C-Metro
Product Or Component Type	Socket-outlet
Switch Function	1-pole
Outlet Poles Configuration	2P with shutters
Outlet Standard	GB 2099.1 GB 16915.1
Colour Tint	Grey silver

### Complementary

Wiring Device Mounting	Surface Flush
Rated Current	10 A at 250 V AC 50/60 Hz
Material	Brass: metal parts Nylon: shutter Polycarbonate: plastic part Steel: metal parts
Load Type	Resistive
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	20 mm

### Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	GB 16915.1 GB 2099.1

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	8.7 cm

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Package 1 Length	8.7 cm
Package 1 Weight	77 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	630 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	7300 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information [Yes](#)

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations