# Product data sheet

Specifications



## Non-Reversing Starter Size 3, 3-Pole, Melting Alloy Overload, NEMA 1 +Options

8536SEG1V84CFF4TX22Y59

Discontinued

## Main

| | |
|---|---|
| **Product Type** | Starter |
| **Product Range** | S |
| **Starter Type** | Non reversing |

## Complementary

| | |
|---|---|
| **Nema Size** | 3 |
| **Rated Current** | 90 A |
| **Number Of Poles** | 3P |
| **Maximum Voltage Rating** | 600 V AC |
| **Phase** | 3 phase |
| **Type Of Overload** | Melting alloy 3 |
| **Horsepower Rating** | 25 HP 200 V AC<br>30 HP 230 V AC<br>50 HP 460 V AC<br>50 HP 575 V AC |
| **Coil Voltage** | 120 V AC 60 Hz secondary circuit<br>208 V AC 60 Hz primary circuit |
| **Control Circuit Type** | Control circuit transformer |
| **Control Units** | Selector switch (HAND-OFF-AUTO) |
| **Auxiliary Contacts** | 2 NO + 2 NC |
| **Other Equipment** | 2 fuses (primary), 1 fuse (secondary) |
| **Terminal Type** | Screw clamp terminals |

## Environment

| | |
|---|---|
| **Enclosure Type** | NEMA 1 painted sheet steel |
| **Certifications** | NEMA<br>UL Listed<br>CSA |

## Ordering and shipping details

| | |
|---|---|
| **Category** | 21193-8502,36 SE,SF(NOT S*R,T,W) |
| **Discount Schedule** | CP1 |
| **Returnability** | No |
| **Country Of Origin** | MX |

Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Contractual warranty

| | |
|---|---|
| **Warranty** | 18 months |