# **Product datasheet**

Specification





# 115V/240V 20VA Universal shaver unit, Vertical, Matt black

E82T727V\_MB\_G1

#### Main

| Range                         | Pieno                      |  |
|-------------------------------|----------------------------|--|
| Product Or Component Type     | Universal shaver           |  |
| Device Application            | Power supply               |  |
| Installation Direction        | Vertical                   |  |
| Input Voltage                 | 240 V AC 50 Hz             |  |
| Output Voltage                | 115 V AC 50 Hz             |  |
| Transformer Rated Power In Va | 20 VA                      |  |
| Load Type                     | Non-polarised<br>Polarised |  |
| Cover Frame Colour Tint       | Matt black                 |  |

## Complementary

| Material | Polycarbonate: surround<br>Polycarbonate: grid plate |
|----------|--|
| Width    | 147 mm   |
| Height   | 87 mm  |
| Depth    | 49.7 mm  |

#### **Environment**

| Ambient Air Temperature For<br>Operation | -540 °C       |
|--|---------------|
| Relative Humidity                        | 095 %         |
| Standards                                | IEC 61558-2-5 |

## **Packing Units**

| Unit Type Of Package 1       | PCE     |
|------------------------------|---------|
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 4.94 cm |
| Package 1 Width              | 14.7 cm |
| Package 1 Length             | 8.7 cm  |
| Package 1 Weight             | 577.5 g |
| Unit Type Of Package 2       | CAR     |
| Number Of Units In Package 2 | 20      |
| Package 2 Height             | 16.3 cm |

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

| Package 2 Width              | 33.0 cm    |  |
|------------------------------|------------|--|
| Package 2 Length             | 50.4 cm    |  |
| Package 2 Weight             | 11550.0 g  |  |
| Unit Type Of Package 3       | PAL        |  |
| Number Of Units In Package 3 | 400        |  |
| Package 3 Height             | 65.2 cm    |  |
| Package 3 Width              | 83.4 cm    |  |
| Package 3 Length             | 108.0 cm   |  |
| Package 3 Weight             | 248000.0 g |  |



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

| <b>⊘</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>Ø</b> | Toxic Heavy Metal Free     |     |
| <b>⊘</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration                        |
|--------------------------|--|
| Eu Rohs Directive        | Compliant EU RoHS Declaration            |
| China Rohs Regulation    | China RoHS declaration                   |
| Environmental Disclosure | Product Environmental Profile            |
| Circularity Profile      | No need of specific recycling operations |