Product data sheet

Specifications

Discontinued

COMBO STARTER 600VAC 810A NEMA

8539SJA51V86S

Main

Contactor Application	Non-reversing
Device Short Name	S

Complementary

Rated Current	810 A
Device Mounting	Surface
Maximum Horse Power Rating	500 hp 575 V AC
Nema Size	7
Number Of Poles	3
Number Of Thermal Units Required	3
Primary Voltage	600 V AC 60 Hz
Product Destination	Circuit breaker MAL3680044M
Reset	With external
Secondary Voltage	120 V AC 60 Hz
Short-Circuit Protection	30000 A AIR

Environment

Nema Degree Of Protection	NEMA 12
Product Certifications	UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21216-8538,39 SH,SJ(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	700.00 lb(US) (317.515 kg)

Contractual warranty

Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty	18 months