Product datasheet

Specifications





AvatarOn, push button for doorbell, 10A, 250V, Metal Gold Hairline

E8331BPL1_GH

Main

Product Or Component Type	Push-button
-	
Device Application	Doorbell
Colour Tint	Metal gold hairline
Colour Tint	Metal gold hairline

Complementary

Device Presentation	Complete product	
Rated Current	10 A at 250 V AC 50/60 Hz	
Number Of Gangs	1 gang	
Number Of Rocker	1	
Clamping Connection Capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)	
Connections - Terminals	Brass terminal	
Material	Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: frame Polycarbonate + GF 20 %: actuator	
Marking	Bell symbol	
Device Mounting	Surface Flush	
Width	86 mm	
Height	86 mm	

Environment

Ip Degree Of Protection	IP20	
Maximum Ambient Air Temperature For Operation	45 °C	
Operating Altitude	2000 m	
Relative Humidity	095 %	
Environmental Characteristic	UV resistant	
Standards	MS IEC 60669-1 SS 227-1 BS EN 60669-1 IEC 60669-1	

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	81.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	60
Package 2 Height	21.0 cm
Package 2 Width	30.0 cm
Package 2 Length	39.5 cm
Package 2 Weight	5.636 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations