Product data sheet

Specifications

Green Premium™

Acti9 - comb busbar - 3L - 18 mm pitch - 12 modules - 100A

A9XPH312

Product availability: Stock - Normally stocked in distribution facility

Price*: 82.08 USD

Main

Range	Acti9
Product Or Component Type	Comb busbar
Mounting Mode	Horizontal
Accessory / Separate Part Category	Connection accessory
Lines Description	3L
Length In 18 Mm Modules	12

Complementary

Number Of Ways	4 ways 3 L
Poles Configuration For 1 Way	1 x 3P
Connection Pitch	0.71 in (18 mm)
Connector Type	tooth
Distance Between Way	2.13 in (54 mm)
Marking	L1 L2 L3
Insulation	Insulated
Device Presentation	Cuttable
[Ie] Rated Operational Current	100 A 104 °F (40 °C)
[Ue] Rated Operational Voltage	415 V AC
[Ui] Rated Insulation Voltage	500 V AC IEC 61439-2
Mounting Location	Top or bottom tunnel type terminals Top or bottom double terminal
9 Mm Pitches	24
Width	8.66 in (220 mm)
Color	White RAL 9003)
Range Compatibility	Acti 9 Acti9 iC60 Acti 9 Acti9 iK60 Acti 9 Acti9 iID Acti 9 Acti9 iID K Acti 9 Acti9 iSW Acti 9 Acti9 iSW-NA Multi9 Multi9 C60

Environment

Standards	IEC 60947-7-1 IEC 61439-2

Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Fire Resistance	1760 °F (960 °C) 30 s) IEC 60695-2-1
Pollution Degree	3 IEC 60947-7-1
Ip Degree Of Protection	IP20 with end-pieces and tooth covers

Ordering and shipping details

Category	US10DE201078
Discount Schedule	0DE2
Gtin	3606480485046
Returnability	Yes
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3 cm)
Package 1 Width	0.63 in (1.6 cm)
Package 1 Length	8.35 in (21.2 cm)
Package 1 Weight	3.81 oz (108 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	2.36 in (6 cm)
Package 2 Width	3.39 in (8.6 cm)
Package 2 Length	9.76 in (24.8 cm)
Package 2 Weight	21.41 oz (607 g)
Unit Type Of Package 3	S03
Number Of Units In Package 3	80
Package 3 Height	11.81 in (30 cm)
Package 3 Width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	22.47 lb(US) (10.19 kg)

Contractual warranty

Warranty	18 months

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO_2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >

Transparency RoHS/REACh

Well-being performance

- Reach Free Of Svhc
- Toxic Heavy Metal Free
- Mercury Free
- Rohs Exemption Information — Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations