

Product datasheet

Specifications



Mechanical Curtain switch,
AvatarOn C, 10A, with fluorescent
Locator, dark grey

E8732CF_DG

Main

Range Of Product	AvatarOn C
Product Or Component Type	Switch
Device Application	Ventilation
Load Type	Curtain control system
Colour Tint	Dark grey

Complementary

Device Presentation	Complete product
Rated Current	10 A at 250 V AC 50/60 Hz
Switch Function	Curtain
Connections - Terminals	Screw terminal
Local Signalling	With light indicator, fluorescent
Material	PC (polycarbonate)
Device Mounting	Surface Flush
Width	86 mm
Height	86 mm
Depth	35.9 mm
Embedding Depth	23.8 mm

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	81 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	9.3 cm
Package 2 Width	12.5 cm
Package 2 Length	26.5 cm
Package 2 Weight	743 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	72
Package 3 Height	29.2 cm
Package 3 Width	29.8 cm
Package 3 Length	39.8 cm
Package 3 Weight	7.287 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance



Sustainable Packaging

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes



Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations