# Product data sheet

Specifications

## Floor standing polyester enclosure, Thalassa PLA, glazed door, completely sealed, 1500x1250x620mm, IP65, IK08

NSYPLA15126TG

**Product availability: Non-Stock - Not normally stocked in distribution facility**

**Price*: 2,967.00 USD**

## Main

| | |
|---|---|
| **Range** | Thalassa |
| **Product Name** | Thalassa PLA |
| **Enclosure Type** | Multi-purpose |
| **Product Or Component Type** | Suitable enclosure |
| **Version** | PLA |
| **Nominal Height** | 59.06 in (1500 mm) |
| **Nominal Width** | 49.21 in (1250 mm) |
| **Nominal Depth** | 24.41 in (620 mm) |
| **Enclosure Mounting** | Floor-standing |
| **Device Composition** | 1 top part<br>1 bottom part<br>2 side part<br>2 door<br>2 rear panel |

## Complementary

| | |
|---|---|
| **Body Type** | Sealed top and bottom part assembled with side parts |
| **Door Type** | Transparent front |
| **Number Of Doors** | 2 |
| **Door Opening Side** | Right and left 120 °) |
| **Lock Type** | 4 points lock, 5 mm double-bar |
| **Accessibility For Operation** | Rear<br>Front |
| **Removable Parts** | Door by hinges<br>Rear panel by fixing element |
| **Material** | polyester reinforced with fibreglass |
| **Color** | Gray RAL 7035) |
| **Standards** | IEC 62208<br>UL 508 A |
| **Nema Degree Of Protection** | NEMA 12<br>NEMA 2<br>NEMA 13<br>NEMA 1 |

Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---|---|
| **Product Certifications** | UL/cUL listed<br>Veritas<br>DNV Marine |
| **Electrical Insulation Class** | Class II |

## Environment

| | |
|---|---|
| **Ip Degree Of Protection** | IP65 IEC 60529 completely sealed) |
| **Ik Degree Of Protection** | IK08 IEC 62262 glazed door) |
| **Fire Resistance** | 1760 °F (960 °C) IEC 62208 |
| **Ambient Air Temperature For Storage** | -31…194 °F (-35…90 °C) |

## Ordering and shipping details

| | |
|---|---|
| **Category** | US10ES180035 |
| **Discount Schedule** | 0ES1 |
| **Gtin** | 3606485434506 |
| **Returnability** | No |
| **Country Of Origin** | ES |

## Packing Units

| | |
|---|---|
| **Unit Type Of Package 1** | PCE |
| **Number Of Units In Package 1** | 1 |
| **Package 1 Height** | 60.24 in (153.0 cm) |
| **Package 1 Width** | 50.39 in (128.0 cm) |
| **Package 1 Length** | 25.59 in (65.0 cm) |
| **Package 1 Weight** | 213.85 lb(US) (97.0 kg) |

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-$CO_2$ products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >

Transparency RoHS/REACh

## Well-being performance

Mercury Free

Rohs Exemption Information Yes

## Certifications & Standards

| | |
|---|---|
| **Reach Regulation** | REACh Declaration |
| **Eu Rohs Directive** | Pro-active compliance (Product out of EU RoHS legal scope) |
| **China Rohs Regulation** | China RoHS declaration<br>Product out of China RoHS scope. Substance declaration for your information. |
| **Environmental Disclosure** | Product Environmental Profile |
| **Circularity Profile** | No need of specific recycling operations |