

Product datasheet

Specifications



Switched socket, Ultimate Screwless flat plate, 1P, screw terminal, IP20, chrome

GU3410BPC

⚠ Discontinued on: 27 Mar 2023

⚠ To be discontinued

Main

| | |
|---------------------------|------------------------|
| Range | Ultimate |
| Device Application | Power supply |
| Aesthetic Name | Screwless flat plate |
| Product Or Component Type | Switched socket |
| Rated Current | 13 A at 230 V AC 50 Hz |
| Fixing Mode | By screws M3.5 x 30 mm |
| Colour Tint | Chrome |

Complementary

| | |
|-----------------------------|------------------------|
| Device Presentation | Complete product |
| Outlet Poles Configuration | 1P |
| Outlet Standard Description | 3 pins |
| Outlet Standard Deviation | British |
| Actuator | Rocker |
| Number Of Gangs | 1 gang |
| Earth Circuit | Standard earth |
| Pilot Light | Without neon indicator |
| Device Mounting | Wall mounted |
| Connections - Terminals | Screw terminal |
| Material | Stainless steel |
| Quantity Per Set | Set of 1 |
| Height | 88 mm |
| Width | 88 mm |
| Depth | 30 mm |
| Socket Number | 1 |
| Mounting Mode | Horizontal |

Environment

| | |
|-------------------------|------|
| Ip Degree Of Protection | IP20 |
| Standards | BS |

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4 cm |
| Package 1 Width | 9.5 cm |
| Package 1 Length | 9.5 cm |
| Package 1 Weight | 210 g |
| Unit Type Of Package 2 | CAR |
| Number Of Units In Package 2 | 100 |
| Package 2 Height | 21.5 cm |
| Package 2 Width | 42 cm |
| Package 2 Length | 49.5 cm |
| Package 2 Weight | 21.72 kg |
| Unit Type Of Package 3 | PAM |
| Number Of Units In Package 3 | 1600 |
| Package 3 Height | 102.5 cm |
| Package 3 Width | 100 cm |
| Package 3 Length | 120 cm |
| Package 3 Weight | 367.52 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | |
|--|--|
|  Rohs Exemption Information | Yes |
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration |