Bảng thông số sản phẩm

Thông số kỹ thuật

Micrologic 2.0 trip unit - LI - for NS 630b..1600 / NS 1600b..3200

33504

Main

Range	ComPacT
Range Of Product	ComPacT NS630b...1600 new generation
Product Or Component Type	Trip unit
Trip Unit Name	MicroLogic 2.0
Trip Unit Technology	Electronic
Range Compatibility	ComPacT new generation NS630b...1600
Device Application	Distribution
Number Of Poles	4P 3P
Protected Poles Description	4t 3t 3t + N/2
Trip Unit Protection Functions	Basic protection
Protection Type	for overload protection (long time) for instantaneous short-circuit protection
Trip Unit Rating	630 A at 50 °C 800 A at 50 °C 1000 A at 50 °C 1250 A at 50 °C 1600 A at 50 °C 2000 A at 50 °C 2500 A at 50 °C 3200 A at 50 °C
Network Type	AC
Network Frequency	50/60 Hz
Circuit Breaker Mounting Mode	Fixed Drawout

Complementary

Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.4...1 x In
Long-Time Protection Delay Adjustment Type Tr	Adjustable 9 settings
[Tr] Long-Time Protection Delay Adjustment Range	0.7…16.6 s at 7.2 x Ir 0.5…24 s at 6 x Ir 12.5…600 s at 1.5 x Ir
Thermal Memory	20 mn
Instantaneous Protection Pick-Up Adjustment Type Ii	Adjustable 9 settings

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

[Ii] Instantaneous Protection Pick-Up Adjustment Range	1.5...10 x Ir
Earth-Leakage Protection	Without
Zone Selective Interlocking Zsi	Without
Local Signalling	3 LEDs (red) for electrical fault 1 LED (red) for internal error

Environment

Ambient Air Temperature For Operation	-25…70 °C
Ambient Air Temperature For Storage	-50…85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.500 cm
Package 1 Width	13.500 cm
Package 1 Length	38.000 cm
Package 1 Weight	306.000 g
Unit Type Of Package 2	P12
Number Of Units In Package 2	32
Package 2 Height	45.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	28.192 kg

Contractual warranty

Warranty	18 months

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO_2 thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

Tìm hiểu thêm về Green Premium >

Hướng dẫn đánh giá về sự bền vững của sản phẩm >

Minh bạch RoHS/REACh

Hiệu suất sức khoẻ

Mercury Free	
Rohs Exemption Information	Yes
Pvc Free	

Chứng nhận & Tiêu chuẩn

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information