Product datasheet

Specifications

Cover frame, Vivace, 1 gang, for switched and unswitched socket, brown

KB_01_BR

Discontinued on: 15 Apr 2024

Discontinued

Main

Range	Vivace
Product Or Component Type	Cover frame
Accessory / Separate Part Category	Fixing accessory
Device Application	Wiring device adaptation
Colour Tint	Wall: brown (Pantone 8580C)

Complementary

Product Destination	Wiring device
Fixing Mode	By clipping locks
Range Compatibility	Vivace cover frame
Number Of Gangs	1 gang
Surface Finish	Painted
Material	Polycarbonate: surround
Surface Treatment	Painted
Projecting Depth	8 mm
Device Mounting	Flush
Width	86 mm
Height	86 mm
Depth	8 mm
Ip Degree Of Protection	IP20

Environment

Standards	BS 5733
Ambient Air Temperature For Operation	-5…40 °C
Ambient Air Temperature For Storage	0…60 °C
Relative Humidity	0…95 %
Operating Altitude	0...2000 m
Environmental Characteristic	Indoor use

Packing Units

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.8 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	20 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	40
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	872 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	400
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	8330 g

Contractual warranty

Warranty	18 months

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO_2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >

Transparency

RoHS/REACh

Well-being performance

Reach Free Of Svhc	
Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations