Product data sheet

Specifications

APC Back-UPS Pro 1000VA, 120V

BP1000

Discontinued on: Jun 10, 2022

Discontinued

Overview

Lead Time	Usually in Stock

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Rated Power In W	670 W
Rated Power In Va	1000 VA
Input Connection Type	NEMA 5-15P
Output Connection Type	6 NEMA 5-15R
Number Of Rack Unit	0U
Cable Length	1.83 m
Number Of Cables	1
Battery Type	Lead-acid battery
Provided Equipment	User manual

Batteries & Runtime

Run Time	View Runtime Graph
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	3.3 h
Number Of Battery Replacement Quantity	1
Replacement Battery	RBC6

Physical

Colour	Beige
Height	21.6 cm
Width	17 cm
Depth	43.9 cm
Net Weight	19.36 kg
Mounting Location	Front

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No

Input

Network Frequency	50/60 Hz +/- 3 Hz auto-sensing
Input Voltage Limits	88...148 V

Output

Maximum Configurable Power In W	670 W
Ups Type	Line interactive

Conformance

Product Certifications	CSA
Equipment Protection Policy	Lifetime : $150000

Environmental

Ambient Air Temperature For Operation	0…40 °C
Relative Humidity	0…95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-15…45 °C
Storage Relative Humidity	0…95 %
Storage Altitude	0.00…15240.00 m
Acoustic Level	50 dBA

Communications & Management

Free Slots	0
Control Panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge Energy Rate	320 J
Noise Suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	35.6 cm
Package 1 Width	31.8 cm
Package 1 Length	58.4 cm

Package 1 Weight	21.365 kg

Contractual warranty

Warranty	2 years repair or replace