Product datasheet

Specifications





Ulti - 250V 16 AX - 1 gang - 2 way - impress switch module - blue LED

U201SPM_2_B00

() Discontinued on: 20 Jun 2023

① Discontinued

Main

Range	Ulti
Device Application	Control
Product Or Component Type	Switch module
Load Type	Fluorescent
Switch Application	Switch

Complementary

complementary	
Bulb Type	LED blue
Rated Current	16 AX at 220250 V AC 50/60 Hz
Number Of Cables	3 cable(s) 2.5 mm ²
Opening Distance	> 3 mm
Device Mounting	Flush Surface
Fixing Mode	By screws
Distance Between Centers	60.3 mm
Operating Mode	Manual
Number Of Gangs	1 gang
Switch Function	2-way
Width	87 mm
Height	87 mm
Depth	23.3 mm

Environment

Ambient Air Temperature For Operation	035 °C
Ambient Air Temperature For Storage	℃ 00…0
Relative Humidity	095 %
Standards	BS EN 60669-1 IEC 60669-1
Environmental Characteristic	No UV resistant
Ip Degree Of Protection	IP2X
Operating Altitude	<= 2000 m

Excluding VAT, FCA Jabal Ali & are subject to change - check with your local distributor.

Packing Units

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.1 cm
Package 1 Width	8.4 cm
Package 1 Length	8.6 cm
Package 1 Weight	168.57 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	30
Package 2 Height	18 cm
Package 2 Width	31.2 cm
Package 2 Length	56.3 cm
Package 2 Weight	5057.1 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	600
Package 3 Height	100 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	101142 g

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations