# **Product datasheet**

Specifications





# 130mm Rotating Mirror Red 24VDC

XVR13B04

## Main

Range Of Product	Harmony XVR
Product Or Component Type	Prewired rotating mirror beacon
Sound Signalling	Without
Device Short Name	XVR
Mounting Diameter	130 mm
Ip Degree Of Protection	IP66 (resistant to vibration) conforming to IEC 60529
[Us] Rated Supply Voltage	24 V DC
Light Source	High luminosity LED, red

# Complementary

Material	ABS (acrylonitrile butadiene-styrene): body part PC: globe
Cad Overall Width	130 mm
Cad Overall Depth	130 mm
Net Weight	0.8 kg
Marking	CE
Product Mounting	By 3 M8 screws
Supply Voltage Limits	1930 V DC
[Uimp] Rated Impulse Withstand Voltage	0.8 kV
<b>Current Consumption</b>	125 mA
Flashing Frequency	2.7 Hz
Clamping Connection Capacity	1.25 mm²
Awg Gauge	AWG 18
Cable Length	400 mm

# **Environment**

Standards	IEC 61000-6-2 IEC 61000-6-4
Protective Treatment	TC
Ambient Air Temperature For Storage	-3570 °C
Ambient Air Temperature For Operation	-3050 °C
Electrical Shock Protection Class	Class II conforming to IEC 61140

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

# **Packing Units**

9	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.7 cm
Package 1 Width	18.7 cm
Package 1 Length	26.6 cm
Package 1 Weight	1.214 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	8.488 kg

# **Contractual warranty**

Warranty 18 months



Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

# Well-being performance



Rohs Exemption Information

#### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information


# XVR13B04

## **Dimensions Drawings**

# Rotating Mirror Beacon

#### **Dimensions**





# XVR13B04

Mounting and Clearance

## Rotating Mirror Beacon

#### **Panel Cut-out**

