

Product datasheet

Specifications



Switch actuator REG-K/2x230/16 w. manual mode and current detection, light grey

MTN647395

Price: 655.72 USD

Main

Range Of Product	KNX
Product Or Component Type	Switch actuator
Operating Mode	Manual
Bus Type	KNX
Modular Device Additional Info	Connectable with different phases
Number Of Contacts	2

Complementary

Function Available	Current detection
Total Number Of 18 Mm Modules	2.5
Mounting Support	DIN rail
[Ue] Rated Operational Voltage	100...240 V
Network Frequency	50...60 Hz
[In] Rated Current	0.1...16 A

Load Type

Incandescent lamps: ≤ 3600 W, 230 V AC
Halogen lamps: ≤ 2500 W, 230 V AC
Incandescent lamps: ≤ 1600 W, 100 V AC
Incandescent lamps: ≤ 3840 W, 240 V AC
Halogen lamps: ≤ 1086 W, 100 V AC
Halogen lamps: ≤ 2608 W, 240 V AC
Parallel compensated fluorescent lamp: ≤ 1086 VA, 100 V AC
Parallel compensated fluorescent lamp: ≤ 2500 VA, 230 V AC
Parallel compensated fluorescent lamp: ≤ 2608 VA, 240 V AC
Capacitive: , 16 A, 200 μ F, 100...240 V AC
Motor: ≤ 434 W, 100 V AC
Motor: ≤ 1000 W, 230 V AC
Motor: ≤ 1043 W, 240 V AC

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	7.900 cm
Package 1 Length	9.700 cm
Package 1 Weight	218.000 g

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Unit Type Of Package 2	CAR
Number Of Units In Package 2	30
Package 2 Height	19.500 cm
Package 2 Width	30.800 cm
Package 2 Length	40.600 cm
Package 2 Weight	6.948 kg

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile [End of Life Information](#)