Product datasheet

Specification





Enclosure for modular device, Mureva Enclosure, 2x12 modules, earth terminal block

13983

! Discontinued on: 1 Jan 2008

(!) Discontinued

Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for modular device
Mounting Plate Description	Slotted

Complementary

•	
Enclosure Mounting	Surface
9 Mm Pitches	24
Number Of 18 Mm Modules Per Row	12
Total Number Of 18 Mm Modules	24
Number Of Horizontal Rows	2
Electrical Insulation Class	Double insulation Class II
Provided Equipment	2 marking kit 2 wiring strap 1 terminal block 32 holes 1 terminal block support
Type Of Front Cover	Transparent Reversible
Power Dissipation In W	34 W
[In] Rated Current	63 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	17
Number Of Terminal Blocks	1 earth (screw connection) with 32 outgoers
Distribution Block Outgoers	16 x 16 mm² + 16 x 10 mm²
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Width	340 mm
Height	460 mm
Depth	160 mm
Internal Depth	88 mm

Colour Door: transparent green
Enclosure: light grey (RAL 7035)

Environment

Standards	IEC 61439-3 EN 50262 IEC 60695-2-1 IEC 60670	
Fire Resistance	650 °C conforming to IEC 60695-2-1	
Ip Degree Of Protection	IP65 conforming to IEC 60529	
Ik Degree Of Protection	IK09 conforming to EN 50102	
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013	
Overvoltage Category	II	
Ambient Air Temperature For Operation	-2560 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.000 cm
Package 1 Width	36.000 cm
Package 1 Length	47.500 cm
Package 1 Weight	3.316 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	28
Package 2 Height	80.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	106.220 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >








Lower Impact Materials Transparency RoHS/REACh

Resource performance



Well-being performance

Rohs Exemption Information



Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations