

Product datasheet

Specifications



Carriage switch, MasterPact NT/
NW, ComPacT NS, drawout,
chassis disconnected position (CD),
1 NO/NC, standard, 8A/240VAC

33753

Main

Device Short Name	disconnected position contact
Product Or Component Type	Auxiliary contact
Device Application	Monitoring
Range Compatibility	Masterpact MasterPact NT Masterpact MasterPact NW Masterpact MasterPact NW DC ComPact ComPact NS630b...1600
Signal Contacts Composition	1 NO/NC

Complementary

Auxiliary Contacts Type	Standard
Auxiliary Contacts Operation	Disconnected position
Mounting Mode	Drawout
[Ie] Rated Operational Current	AC-12: 6 A at 690 V AC 50/60 Hz AC-12: 8 A at 240 V AC 50/60 Hz AC-12: 8 A at 380 V AC 50/60 Hz AC-12: 8 A at 480 V AC 50/60 Hz DC-12: 0.8 A at 125 V DC DC-12: 2.5 A at 24/48 V DC DC-12: 0.3 A at 150 V DC
Minimum Load	100 mA at 24 V

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	5.000 cm
Package 1 Length	6.000 cm
Package 1 Weight	19.800 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	50
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.190 kg
Unit Type Of Package 3	P12

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	1600
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	50.080 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation		China RoHS declaration
		Product out of China RoHS scope. Substance declaration for your information