# **Product datasheet**

Specifications

Green Premium™



# Elbow, Canalis KSA400, aluminium, 400A, side B made to measure, to go upward, 3L+N+PE, white RAL9001

KSA400DLE41A

#### Main

Mann	
Range Of Product	Canalis
Product Name	KS
Device Short Name	KSA
Offer Type	Advanced
Product Or Component Type	Elbow
Busbar Description	Standard on made to measure (only one side)
Product Compatibility	Canalis KSA busbar trunking 400 A
Device Application	Change direction
Conductors Material	Aluminium
Busbar Trunking Polarity	3L + N + PE
[le] Rated Operational Current	400 A at 35 °C
Ip Degree Of Protection	IP55 conforming to IEC 60529
[Ue] Rated Operational Voltage	230690 V
Network Frequency	50/60 Hz
Operating Angle	90 °
Direction Change Type	direction 1: edgewise to upward - neutral to left
Colour	White (RAL 9001)
Dimension Type	Made to measure

### Complementary

	-	
Length	250 mm for side A 250…750 mm for side B	
Width	54 mm	
Height	146 mm	
Mounting Location	On trunking	
Mounting Position	Any position	
Electrical Connection	Lubricated sliding contact	
Mounting Mode	By screws	
Standards	IEC 61439-1 IEC 61439-6	

### Environment

Ik Degree Of Protection

IK08 conforming to IEC 62262

### **Packing Units**

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	87.0 cm
Package 1 Length	87.0 cm
Package 1 Weight	42.0 kg

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations