Product datasheet

Specifications





ClimaSys, Outlet grille plast cut out 125x125mm ext dim 137x117mm IP54

NSYCAG125LPF

Main

Range	ClimaSys	
Product	ClimaSys CA	
Range Compatibility	ClimaSys ClimaSys CV fan	
Product Or Component Type	Outlet grille	
Accessory / Separate Part Category	Thermal management accessory	
Accessory / Separate Part Destination	ClimaSys ventilation system	
Fixing Mode	Clipped By screws	
Device Composition	1 support frame 1 external part 1 G2 M1 synthetic standard filter	

Complementary

Material	Injected thermoplastic (ASA PC)	
Colour	External part: grey (RAL 7035)	
Cut-Out Dimensions	125 x 125 mm	
Height	External: 170 mm	
Width	External: 150 mm	
Depth	15 mm external:	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	15.5 cm
Package 1 Length	18 cm
Package 1 Weight	220 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	56
Package 2 Height	38.5 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	13 kg

Unit Type Of Package 3	P12
Number Of Units In Package 3	448
Package 3 Height	91 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	119 ka

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations