



TeSys, TeSys VARIO - additional earthing block - 80 A - for V3 / V4

VZ15

Main

Range	TeSys
Device Short Name	VZ
Product Or Component Type	Additional earthing block
Performance Level	High performance
Contacts Type And Composition	Without
Product Compatibility	V3 V4
Network Type	DC AC
Network Frequency	50/60 Hz

Complementary

Mounting Location	Left Right
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	6 kV
[Ith] Conventional Free Air Thermal Current	80 A
Connections - Terminals	Screw clamp terminals
Height	83 mm
Width	20 mm
Depth	46 mm
Net Weight	0.1 kg

Environment

Standards	IEC 60947-3
Product Certifications	UL CSA GL UKCA
Protective Treatment	TC
Ip Degree Of Protection	IP20 conforming to IEC 60529
Mechanical Robustness	Vibrations 10150 Hz (5 gn) conforming to IEC 60068-2-6 Shocks 11 ms (15 gn) conforming to IEC 60068-2-27
Ambient Air Temperature For Operation	-2050 °C
Fire Resistance	960 °C conforming to IEC 60695-2-1

Packing Units

9	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	3.7 cm
Package 1 Length	9.0 cm
Package 1 Weight	79.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	69
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.758 kg

Contractual warranty

Warranty 18 months

20 Apr 2024



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations