Product data sheet

Specifications





Mounting plate, Linergy HK, 3P, 25A 4.4mm², 190x54x61mm

AK5PA232

Main

Range	Linergy
Product Name	НК
Product Or Component Type	Mounting plate
Poles Description	3P
[Ith] Conventional Free Air Thermal Current	25 A
I ² T On Activation	200000 A².s
Number Of Cables	3 0.01 in² (4 mm²) 221 °F (105 °C)
Width	2.13 in (54 mm)
Height	7.48 in (190 mm)
Depth	2.40 in (61 mm)

Complementary

[Ui] Rated Insulation Voltage	690 V IEC 60439-1
9 Mm Pitches	6
Net Weight	0.51 lb(US) (0.23 kg)

Environment

Standards	IEC 60439
Product Certifications	UL DNV CSA LROS (Lloyds register of shipping)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.36 in (6.000 cm)
Package 1 Width	2.95 in (7.500 cm)
Package 1 Length	8.66 in (22.000 cm)
Package 1 Weight	13.23 oz (375.000 g)
Unit Type Of Package 2	\$03
Number Of Units In Package 2	20
Package 2 Height	11.81 in (30.000 cm)

Package 2 Width	11.81 in (30.000 cm)	
Package 2 Length	15.75 in (40.000 cm)	
Package 2 Weight	17.59 lb(US) (7.980 kg)	
Unit Type Of Package 3	P06	
Number Of Units In Package 3	160	
Package 3 Height	29.53 in (75.000 cm)	
Package 3 Width	23.62 in (60.000 cm)	
Package 3 Length	31.50 in (80.000 cm)	
Package 3 Weight	163.94 lb(US) (74.364 kg)	

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations