Product data sheet

Specifications



SWITCH NOT FUSIBLE DT 240V 30A 4P NEMA1

C92451

() Discontinued on: May 12, 2023

(!) Discontinued

Main

Product	Single Throw Safety Switch
Duty Rating	General duty
Disconnect Type	Non-fusible disconnect switch
Factory Installed Neutral	None
Number Of Poles	4
Current Rating	30 A
Voltage Rating	250 V DC 240 V AC
Enclosure Rating	NEMA 1

Complementary

Short-Circuit Current	10 kA H or K
Fuse Type	H or K
Mounting Type	Surface
Wire Size	AWG 12AWG 2 aluminum AWG 14AWG 2 copper
Tightening Torque	35 lbf.in (3.95 N.m) 0.000.01 in ² (2.085.26 mm ²) AWG 14AWG 10) 40 lbf.in (4.52 N.m) 0.01 in ² (8.37 mm ²) AWG 8) 45 lbf.in (5.08 N.m) 0.020.03 in ² (13.321.15 mm ²) AWG 6AWG 4) 50 lbf.in (5.65 N.m) 0.040.05 in ² (26.6733.62 mm ²) AWG 3AWG 2)
Depth	6.38 in (162.05 mm)
Width	17.63 in (447.80 mm)
Height	13.38 in (339.85 mm)
Net Weight	9.04 lb(US) (4.1 kg)

Environment

Certifications	UL listed file E2875

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.39 in (34 cm)
Package 1 Width	17.64 in (44.8 cm)

Package 1 Length

6.38 in (16.2 cm)

Package 1 Weight

9.00 lb(US) (4.082 kg)

2

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile