





Safety switch, heavy duty, fusible, 30A, 240 VAC/250VDC, 3 poles, 7.5hp, NEMA 12, neutral

CH321NAWK

! Discontinued on: Aug 8, 2023

(!) Discontinued

Main

Product	Single Throw Safety Switch
Disconnect Type	Fusible disconnect
Number Of Poles	3
Electrical Connection	Lugs
Duty Rating	Heavy duty

Complementary

Line Rated Current	30 A
Factory Installed Neutral	Neutral (factory installed)
Mounting Type	Surface
Voltage Rating	240 V DC 250 V AC
Motor Power Hp	1.5 hp at 240 V AC 5060 Hz for 1 phase motors 3 hp at 240 V AC 5060 kHz for 3 phases motors 3 hp at 240 V AC 5060 kHz for 1 phase motors 7.5 hp at 240 V AC 5060 kHz for 3 phases motors 5 hp at 250 V DC
Wire Size	AWG 12AWG 6 aluminum AWG 14AWG 6 copper
Tightening Torque	45 lbf.in (5.08 N.m) 0.02 in² (13.3 mm²) AWG 6) 40 lbf.in (4.52 N.m) 0.01 in² (8.367 mm²) AWG 8) 35 lbf.in (3.95 N.m) 0.000.01 in² (2.065.261 mm²) AWG 14AWG 10)
Height	14.6 in (370.84 mm)
Width	6.63 in (168.40 mm)
Depth	4.96 in (125.98 mm)

Environment

Certifications	CSA
Enclosure Rating	NEMA 3R/12 galvannealed steel

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.40 in (13.716 cm)
Package 1 Width	7.70 in (19.558 cm)

Package 1 Length	17.50 in (44.45 cm)
Package 1 Weight	10.45 lb(US) (4.74 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >


Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations