


Product data sheet

Specifications

Cover for cable duct - Width=60mm

AK2CA6



Main

Product Or Component Type	Cover
Accessory / Separate Part Category	Cabling accessories
Range Compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Mounting Support	Cable duct 2.36 in (60 mm)
Quantity Per Set	Set of 8

Complementary

Colour	Blue RAL 5000)
Length	78.74 in (2000 mm)
Width	2.36 in (60 mm)
Material	PVC (polyvinyl chloride)
Net Weight	0.95 lb(US) (0.43 kg)

Environment

Ambient Air Temperature For Operation	23...140 °F (-5...60 °C)
Flame Retardance	V-0 UL 94
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 VDE 0660

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.39 in (1.0 cm)
Package 1 Width	3.94 in (10.0 cm)
Package 1 Length	78.74 in (200.0 cm)
Package 1 Weight	16.12 oz (457.0 g)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	1120
Package 2 Height	42.52 in (108.0 cm)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	79.13 in (201.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	1316.16 lb(US) (597.0 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	8
Package 3 Height	79.13 in (201.0 cm)
Package 3 Width	4.53 in (11.5 cm)
Package 3 Length	2.56 in (6.5 cm)
Package 3 Weight	8.91 lb(US) (4.04 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)