

# Product data sheet

Specifications



## Ethernet ConneXium cable - shielded twisted pair - 2 x rugged RJ45 - UL - 5 m

TCSECU3M3M5S4

### Main

Range Of Product	ConneXium
Accessory / Separate Part Category	Connection accessories
Accessory / Separate Part Type	Connecting cable
Product Or Component Type	Shielded twisted pair straight cable
Accessory / Separate Part Destination	Ethernet network
Cable Length	16.40 ft (5 m)

### Complementary

Transmission Support Medium	Twisted shielded pairs cable
Communication Network Category	5e
Awg Gauge	AWG 24
Electrical Connection	2 connectors, RJ45 straight 8
Marking	UL
Cover Material	PVC

### Environment

Ip Degree Of Protection	IP20
Standards	IEC 11801 class D UL 444 EN 50173 class D CMG FT4 EIA/TIA-568 category CAT 5E

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3.000 cm)
Package 1 Width	7.48 in (19.000 cm)
Package 1 Length	9.06 in (23.000 cm)
Package 1 Weight	10.12 oz (287.000 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	10
Package 2 Height	5.91 in (15.000 cm)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	6.47 lb(US) (2.935 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

<b>Eu Rohs Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
--------------------------	---

<b>China Rohs Regulation</b>	<a href="#">China RoHS declaration</a>
------------------------------	--