

# Product data sheet

Specifications



Disconnect switch, TeSys VLS, protruding rotary handle, screw mounting, 48x48 mm, black handle, 5 mm shaft

VLSH4S5B

## Main

Range	TeSys
Device Short Name	VLSH
Product Or Component Type	Rotary handle
Range Compatibility	TeSys TeSys VARIO LS VLS3P
Handle Colour	Black
Handle Front Plate Colour	Grey
Rotary Handle Padlocking	1 padlock 0.16...0.31 in (4...8 mm)
Marking	0 - 1

## Complementary

Fixing Mode	By 4 screws
Tightening Torque	20.36 lbf.in (2.3 N.m)
Base Dimension	48 x 48 mm
Height	1.89 in (48 mm)
Width	1.89 in (48 mm)
Depth	1.54 in (39 mm)
Net Weight	0.13 lb(US) (0.06 kg)

## Environment

Ip Degree Of Protection	IP65
Nema Degree Of Protection	NEMA 1 NEMA 2 UL 508 NEMA 3R UL 508 NEMA 4 UL 508 NEMA 4X UL 508 NEMA 12 UL 508 NEMA 12K UL 508

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3 cm)
Package 1 Width	3.74 in (9.5 cm)
Package 1 Length	1.97 in (5 cm)
Package 1 Weight	1.34 oz (38 g)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	S02
Number Of Units In Package 2	40
Package 2 Height	5.91 in (15 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	4.35 lb(US) (1.975 kg)

## Sustainability





**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
<b>Reach Regulation</b>	<a href="#">REACH Declaration</a>
<b>Eu Rohs Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
<b>China Rohs Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)